

**FOAMED ACRYLIC TAPE
VST6508G
TECHNICAL DATA**

TECHNICAL DESCRIPTION	UNIT OF MEASUREMENT	TECHNICAL VALUE
CARRIER		ACRYLIC FOAM
ADHESIVE		ACRYLIC
COLOUR		GREY
THICKNESS	mm	0.8
DENSITY OF FOAM	kg/m ³	770
RELEASE LINER		RED SILICONIZED PE FILM
180° PEEL ADHESION ASTM D-3330	g/25mm	3700
TENSILE ADHESION (T-BLOCK TEST) ASTM D-897	g/cm ²	6500
DYNAMIC SHEAR ASTM D-1002	g/cm ²	≥3700 (after 20 mins) ≥6500 (after 24 hours)
TEMPERATURE RESISTANCE SHORT TERM	°C	160
TEMPERATURE RESISTANCE LONG TERM	°C	100
LOW TEMPERATURE RESISTANCE	°C	-40
U.V. RESISTANCE		GOOD

Unless stated otherwise all values given are average. All of the tapes in our range should be thoroughly tested on the substrates in the particular application they are intended for. Hi-Bond Tapes Ltd. will not be responsible for product failure unless full testing has been completed. The customer has to decide on the tapes suitability for the intended application.