

LOGO! TD TEXTDISPLAY, 6 LINES, 3 BACKGROUND COLORS 2
ETHERNET PORTS ACCESSORIES, FOR LOGO! 8



General information

Application/function	Can be used with LOGO! 8 and higher
----------------------	-------------------------------------

Operator control and monitoring

Illuminant	LED
------------	-----

Display

Design of display	FSTN
graphics-enabled	No
Line display	
• Number of lines	6
• Number of characters per line	24

Control elements

Keyboard	
• Keys with LED	No
• System keys	Yes
— Number of configurable system keys	0
• Numeric/alphabetical input	
— Numeric keyboard	No
— Alphanumeric keyboard	No

Installation type/mounting

Wall mounting/direct mounting possible	No
--	----

Supply voltage

Type of supply voltage	AC/DC
Rated value (DC)	12 V; 12 V DC, 12/24 V AC/DC

permissible range, lower limit (DC)	10.2 V
permissible range, upper limit (DC)	28.8 V
Power losses	
Power loss, typ.	1.8 W; Typical
Digital inputs	
Number of digital inputs	0
Interfaces	
Number of RS 232 interfaces	0
Number of other interfaces	0
Industrial Ethernet	
• Number of industrial Ethernet interfaces	2
Interrupts/diagnostics/status information	
Diagnostic messages	
• Diagnostic functions	No
Diagnostics indication LED	
• Status indicator digital input (green)	No
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
FM approval	Yes
KC approval	Yes
Marine approval	
• American Bureau of Shipping (ABS)	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Accessories	
belongs to product	LOGO!
Mechanics/material	
Design of housing	plastic
Dimensions	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Weights	
Weight, approx.	220 g
Scope of supply	

Delivery quantity in pieces

1

last modified:

20.04.2015