



Cut



Heat



Medium Duty

Highly durable cut-resistant gloves with extended knitwrist, for all-round protection

- **Advanced protection:** HyFlex® 11-739 medium-duty gloves feature a blended-yarn liner with INTERCEPT™ Cut Resistance Technology, as well as Kevlar® and stainless steel, for advanced, EN ISO D cut resistance
- **Improved durability:** These cut safety gloves' palm-dipped polyurethane (PU) coating is highly durable, attaining EN level 4 abrasion resistance
- **Strengthened grip:** Their coating also grants wearers excellent grip in both dry and slightly oily conditions
- **Enhanced features:** An extended knitwrist offers wearers added forearm and wrist protection



Industries

- Aerospace
- Automotive
- Transportation
- Construction
- Glass manufacturing
- Machinery and Equipment
- Maintenance
- Metal fabrication

Applications

- Assembling metal parts and components
- Assembly of white goods
- Metalwork, glass processing
- Handling sharp or irregular metal pieces
- Press injection molding

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-739

Dexterity with superb cut resistance for optimal productivity

Key Features

- **Advanced liner with Kevlar® and stainless steel:** Superb cut resistance
- **Polyurethane (PU) coating:** Excellent grip and abrasion resistance
- **Extended knitwrist:** Additional forearm and wrist protection

Performance Standards & Regulatory Compliance



EN388: 2016



4X43D

EN 407



X1XXXX

Technologies



INTERCEPT™
Cut Resistance Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-739	Finishing: Palm dipped Coating Material: Polyurethane Liner Material: HPPE, Stainless steel, Cotton, Nylon, Kevlar®, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	290-340 mm / 11.4-13.38 inches	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell