



Figure similar

## Data sheet for braking resistor

Article No. : **JJY:023422620001**

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

Rated power $P_{DB}$	1.1 kW
Rated power, max. <sup>1)</sup>	22 kW

### General technical specifications

Resistance	25 $\Omega$
DC link voltage	330 ... 840 V
DC-link voltage, max.	840 V

### Mechanical data

Degree of protection	IP21
Net weight	7 kg (15.43 lb)
Dimensions	
Width	220 mm (8.66 in)
Height	180 mm (7.09 in)
Depth	470 mm (18.50 in)

### Standards

Compliance with standards	CE / UL / CSA
---------------------------	---------------

### Connections

Power connection	
Version	Terminal block
Conductor cross-section	10.0 mm <sup>2</sup> (AWG 8)

### Thermostatic switch

Version	integrated
Conductor cross-section	1.5 mm <sup>2</sup> (AWG 16)

### Environmental conditions

Cooling method	natural convection
Ambient temperature in operation	-25 ... 40 °C (-13 ... 104 °F)

<sup>1)</sup>Load duration for peak power 12 s, for a braking duty cycle period of 240 s.