



Productgegevensblad

LUHR 30



Lineaire lagereenheid zonder seals



LUHR
With double lip seal



LUHR
With shaft seals



A [mm]:	50
D = Da [mm]:	40
Fw [mm]:	30
H [mm]:	30
H1 [mm]:	60
H2 [mm]:	29
H3 [mm]:	18
J [mm]:	53
L [mm]:	67
N [mm]:	6.6
N1:	M8
Kogelbanen [#]:	8
Cdyn [N]:	3150

Datum: 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

Productgegevensblad

LUHR 30

Lineaire lagereenheid zonder seals

C0 [N]:	2700
Gewicht [kg]:	0.37
A1[mm]:	59
C1[mm]:	58

Datum: 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.