


# VARTA LITHIUM Cylindrical CR123A OEM



Premium product for use in a wide array of professional electronic devices. Provides reliable, long-lasting energy.



## Information

- Guaranteed storage time of 10 years
- Battery type in Top 10 bestselling special batteries
- Operation over wide temperature range
- Matt finish label and haptic product experience
- VARTA brand quality ensured

## Article Details

Ordernumber	06205 201 501
Customs Tariff Number	85065010
Country Of Origin	China
IEC	CR17345
Others	CR123A, CR123A
System	Lithium
Voltage	3.00
Consumer Unit	1
Packaging Information	OEM
DG Profile	Lithium metal battery UN3090 (to 1g / 8 cells)

## Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 520657				0.02
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	400	40 08496 520664	315.00	370.00	58.00	6.62
PAL (Pallet)	36000	40 08496 520671	800.00	1,200.00	1,020.00	616.80
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
15	6		90		400	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany  
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

