



HIGH-POWER HEX. CHIPPER HAMMER

11 MM

RC293H

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:42





DESCRIPTION

HIGH-POWER HEX. CHIPPER HAMMER 11 MM

POWERFUL The design of the two in-line impact pads coupled with a coated piston makes it possible to develop a high level of power. Traditional tool for your chiselling jobs. Progressive trigger. Comfortable sheathed handle insulating against the cold. Includes a metal retention ring - ref. RA293.

STANDARDS / DIRECTIVES

2006/42/CE

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:42



SPECIFIC DATA

Designation	HIGH-POWER HEXAGONAL CHIPPING HAMMER 11 MM
Sales reference	RC293H
Weight (g)	1900
l (mm)	55
L (m)	190
h (mm)	160
Piston stroke mm	66
Vibration (m/s²)	8
Noise level (dBa)	92
C mm	6,3
C min mm	1/4
C mm	3 200
C mm	11 hex
Aluminium rivet maximum diameter mm	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:42

