



Brand of NTN corporation

Technical data

UKFC217H

Bearing units




Grey cast housing, radial insert ball bearing with adapter sleeve, seal with slinger

KIT CONTENT

UK217G2H, FC217

VISUAL (S)



PRODUCT DEFINITION

| | |
|--|-------|
| Brand | SNR |
| A - Housing height | 63 mm |
| A1 - Housing foot height / flange height | 20 mm |
| A2 - Total height from mounting surface | 58 mm |
| A4 - Housing height from mounting surface | 45 mm |
| B - Width of Inner Ring | 44 mm |



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

| | |
|---|--------|
| B1 - Overall width Inner Ring | 82 mm |
| d - Shaft diameter | 75 mm |
| d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve | 110 mm |
| e - Distance mounting surface to bearing center | 18 mm |
| G - Grease fitting | M10x1 |
| H3 - Centering dia | 180 mm |
| J - Mounting holes distance | 208 mm |
| L - Housing width / diameter | 250 mm |
| N - Mounting hole dimension | 23 mm |
| s1 - Distance nut to middle of bearing raceway | 40 mm |

PRODUCT PERFORMANCE

| | |
|-----------------------------------|-------------|
| C - Dynamic load rating | 83200000 mN |
| C0 - Static load rating | 63800000 mN |
| Operating temperature min. | 253,15 °K |
| Operating temperature max. | 373,15 °K |

OTHER FEATURES

| | |
|-----------------------------------|----------|
| Mass | 10,98 kg |
| Adapter sleeve designation | H2317 |

