

AF140-40-11B-13

General Information

Extended Product Type:	AF140-40-11B-13
Product ID:	1SFL447102R1311
EAN:	7320500505205
Catalog Description:	AF140-40-11B-13 Contactor



Categories

Products » Low Voltage Products and Systems » Control Products »
 Contactors » Block Contactors

Ordering

EAN:	7320500505205
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85364900

Dimensions

Product Net Width:	120 mm
Product Net Depth:	128,1 mm
Product Net Height:	150 mm
Product Net Weight:	1.97 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Gross Weight:	2.17 kg

Environmental

Ambient Air Temperature:	Close to Contactor Fitted with Thermal O/L Relay (0.85 - 1.1 Uc) -25...+50 °C Close to Contactor without Thermal O/L Relay (0.85 - 1.1 Uc) -40...+70 °C Close to Contactor for Storage -40...+70 °C
Maximum Operating Altitude Permissible:	3000 m

Technical

Rated Operational Power AC-3 (P_g): (220 / 230 / 240V) 37 kW
 (380 / 400V) 75 kW
 (415V) 75 kW
 (440V) 90 kW

Rated Operational Current AC-1 (I_g): (690V) 40°C 200 A
 (690V) 60°C 175 A
 (690V) 70°C 160 A

Number of Main Contacts NO: 4

Number of Main Contacts NC: 0

Number of Auxiliary Contacts NO: 1

Number of Auxiliary Contacts NC: 1

Rated Control Circuit Voltage (U_c): 50 Hz 100...250 V
 60 Hz 100...250 V
 DC Operation 100...250 V

Coil Consumption: Pull-in at Max Rated Control Circuit Voltage 50Hz 130 V·A
 Pull-in at Max Rated Control Circuit Voltage 60Hz 130 V·A
 Holding at Max Rated Control Circuit Voltage 60Hz 6 V·A
 Holding at Max Rated Control Circuit Voltage 50Hz 6 V·A
 Holding at Max Rated Control Circuit Voltage DC 3 W
 Pull-in at Max Rated Control Circuit Voltage DC 135 W

Technical UL/CSA

Maximum Operating Voltage UL/CSA: Main Circuit 600 V