

PRODUCT-DETAILS

# GSC187NP

## OUTER SLEEVE .187ID NICKEL PLATED



### General Information

Extended Product Type	GSC187NP
Product ID	7TAI029670R0110
EAN	5414363934530
Catalog Description	OUTER SLEEVE .187ID NICKEL PLATED
Long Description	Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .187 Inches/4.75mm, Outer Diameter .227 Inches/5.76mm, Color Orange, Soft Bronze, Nickel Plated

### Ordering

EAN	5414363934530
UPC	786210947617

### Dimensions

Product Net Length	0, mm
--------------------	-------

### Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	3 in 76 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	3.5 in 89 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	6.5 in 165 mm
Package Level 2 Height	3.62 in 92 mm
Package Level 2 Depth / Length	16.12 in 409 mm

### Additional Information

Application	for Grounding, Terminating and Insulating Shielded and Coaxial Cable
Brand / Label	Sta-Kon
Color	Orange
Effective Date	20041214
Material	Soft Bronze
Number of Batteries	0
Product Name	ELECTRICAL CONNECTOR, <1000V
Product Type	Two-Piece Outer Sleeve Connector

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GSC187NP
Instructions and Manuals	GSC187NP

### Classifications

ETIM 6	EC002650 - Connection for screened wires
ETIM 7	EC002650 - Connection for screened wires
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

