



Product-Nr.	156310-01
EAN:	4260556627359
Model:	TUBELED_70 EVO DC
Order number:	156310-01
Model:	TUBELED_70 EVO DC
Illuminant:	SMD LED
Power consumption:	37 W
Lamp luminous flux:	5697 lm
Lamp luminous efficiency:	155 lm/W
Light colour:	5600K 3-step MacAdam
Number of poles:	3
Connected load:	24V DC $\pm$ 10%
Power supply:	external
Connection (connector):	M12 A-coded
Degree of protection:	IP67/IP69K
Class of protection:	III
Glare control:	diffuser film
Beam angle (optics):	100°
Operating temperature:	-30 °C - +70 °C (-22 °F - 158 °F)
Storage temperature:	-20 °C - +80 °C (-4 °F - 176 °F)
Colour rendering (Ra):	>85
Lamps lifetime:	> 100,000 h (L80/B10)
Housing material:	Aluminum, glass
Height [B] x Width [C]:	59,5 mm x 70 mm (~2,34" x ~2,76")
Length [A]:	790 mm (~31,1")
Weight (net):	2200 g (~78 oz)
Gross weight:	2670 g (~94 oz)
Risk group (DIN EN 62471):	free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	optional via accessories
Mounting accessories:	optional
Made in:	Germany