



Pushing Performance
Since 1945

Han 24HPR-HSMA2-SL-M40-enlarged



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 024 0954
Specification	Han 24HPR-HSMA2-SL-M40-enlarged
HARTING eCatalogue	https://harting.com/19400240954

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR enlarged
Type of hood/housing	Surface mounted housing
Description of hood/housing	Horizontal version

Version

Size	24 HPR enlarged
Version	Top entry
Number of cable entries	2
Cable entry	2x M40
Field of application	Hoods/housings for harsh outdoor environments
Details	Bulkhead mounted housing 09 40 024 0368 not included, please order separately
Details	When using Han [®] Standard inserts of size B or Han-Modular [®] hinged frames, please order adapter 09400009961 separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	645 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140173415
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466