



ATUM-12/4-0-100MM

SHRINK TUBE WITH ADHESIVE, 3:1, ID=12mm BLACK, DIE-CUT, L=100mm, THIN-W



Product Properties:

Model	Thin-walled
Operating temperature	-55-110 °C
Transparent	No
Type	Heat-shrink
Shrink rate	3:1
With inner glue	Yes
Printable	No
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	No

Dimensions:

Wall thickness after shrinking	1.78 mm
MOQ	1000 .
Unit	pcs
Length	0.1 m
Inner diameter before heat-shrink	12 mm
Inner diameter after heat-shrink	4 mm

Approvals:

UL approval	Yes
With approval according to UL	Yes

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
Link to manufacturer COC	https://www.te.com/commerce/alt/SinglePartSearch.do?PN=NB09056001
PFAS	No PFAS
REACH	Yes. CAS 119-47-1, < 4 %
RoHS	RoHS 3 (2015/863)
SCIP	fd533c22-e3af-46cd-aebc-2c5ece4d2d24
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000217 - Shrink tubing
ETIM-Release	10.0
Trademark	TE Connectivity
Product Group	Die-Cut
Search Description	5509106119
Alternative SKU	ATUM-12/4-0-100MM

Logistic information:

Barcode	733117615293
Country of origin	CZ
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1000 .
Stock code	ATUM-12/4-0-100MM
Taric code	39173200
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.