

M12-ADPT-M12/M12-8/4P-YCOD-F/F/F-STR



Image is for illustration purposes only. Please refer to product description.

Part number	21 43 361 9800
Specification	M12-ADPT-M12/M12-8/4P-YCOD-F/F/F-STR
HARTING eCatalogue	https://harting.com/21433619800

Identification

Category	Accessories
Series	Circular connectors M12
Connector 1	Female
Connector 2	Female
Connector 3	Female
Type of accessory	T-splitter

Version

Gender	Male Female
Shielding	Shielded
Number of contacts	8
Number of data contacts	4
Number of power contacts	4
Coding	Y-coding

Technical characteristics

Rated voltage	30 V DC
Rated impulse voltage	0.8 kV
Rated current (data)	0.5 A
Rated current (power)	4 A
Transmission characteristics	Cat. 5
Limiting temperature	-25 ... +85 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP54

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61076-2-101
PROFINET	Yes

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140236707
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400