



metal
FREE

HAVOC
DM20184

S3 CI SRC
EN ISO 20345:2011
35 to 47

Low shoe
Putek® textile

HYPERTEX
- PUTEK TECHNOLOGY -

STARK®

3D Lining

Light
PLUS

PLUS
VENTO

FLEXsystem
ZERO

- Ⓢ Black and grey sporty urban safety shoes, extremely lightweight.
- Ⓢ Putek® textile upper, high resistance to abrasion, heel in **Stark®** anti-abrasion.
- Ⓢ **3D.LINING®** in three-ply material for improved evacuation of moisture to the exterior, high breathability and fast-drying.
- Ⓢ Vamp lining in non-woven fabric. Resists abrasion and acid perspiration.
- Ⓢ Padded collar. Provides comfort to the ankle-bones and protects the Achilles tendon.
- Ⓢ Lace up by laces 100 cm.
- Ⓢ Padded tongue to provide better protection to the instep, combined with two side gussets to prevent grit from entering the shoe.
- Ⓢ Complete **VENTO-PLUS®** anatomical and antistatic inlay, with honeycomb structure for improved air circulation.
- Ⓢ Stab-proof non-metallic **FLEX-SYSTEM®** liner : total protection of the sole of the foot.
- Ⓢ **LIGHT-PLUS®** protective toecap in synthetic material offering protection from an impact of 200 J.

DIAMONT Sole in PU dual density **BASF** last generation :

- ▶ Resists oils and hydrocarbons
- ▶ Linear profile, comfort, lightness and versatility
- ▶ Absorption of heel impact > 20 joules
- ▶ Streamlined profile rising towards the toes



Slip resistance tests results

EN Standard : EN ISO 20345 : 2011 **Requirement SRC**
(SRA+SRB)

SRA Test ground : ceramic / lubricant : water and detergent
On flat **0,40** (>0,32) – On the heel **0,40** (>0,28)

SRB Test ground steel / lubricant : glycerine
On flat **0,18** (>0,18) – On the heel: **0,16** (>0,13)

Weight	Gross weight (42) : 1050 g / Net weight (42) : 834 g			
Size	35 to 39	40 to 41	42 to 45	46 to 47
Packaging	5 pairs	10 pairs		5 pairs
Box shoes (mm)	340 x 210 x 133		340 x 245 x 133	
Cartons (mm)	685 x 225 x 359	685 x 440 x 359	685 x 505 x 359	685 x 255 x 359