

## Dreibein-Stativ

### 00004162 "Star 62" Tripod



Highlightstext:

- Camera tripod for non-jerky images and a steady hold on uneven surfaces, suitable for photo and video cameras
- The 3D tilt head allows perfect alignment for landscape and portrait shots
- Quick-release plate for quickly changing the camera
- Spirit level integrated into the tripod head and spirit vial at the base
- With crank for continuous height adjustment of the centre column
- Lockable leg braces and flexible rubber feet for a firm and steady grip on uneven surfaces
- With the functional quick-action leg locks the tripod legs can easily and quickly be fixed at the required height or position
- Handle
- With hook for weighing the tripod down in strong winds and on rough terrain
- Spare quick release plate: Hama item no. 00004154

Technical Details:

- Thread/Connection: 1/4" (6.4 mm)
- Handle: Plastic Grip
- Incl. Tripod Case: Yes
- Leg Segments: 3 Sections (2x Extendible)
- Levelling Device: Yes
- Material: Aluminium
- Maximum Load: 4000 g
- Tripod Head: 3D: 3-Way Head
- Height-Adjustable Centre Column: Geared Centre Column via Crank
- Maximum Profile Thickness: 23 mm
- Min. Height - Max. Height: 64 -160 cm
- Weight: 1500 g
- Colour: Champagne
- Line: Star 62
- Use: Photo/Video (3D)

Scope Of Delivery:

- 1 "Star 62" tripod
- 1 bag

	<b>Brand</b>	<b>Item-no.</b>	<b>VE</b>
	<b>hama</b> <sup>®</sup>	00004162	6