

Bourdon tube pressure gauges, liquid filling,

Modelcode type: 213.53.100

Item number: 82142907

Description	
Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	0...25 MPa
Unit of outer Scale	MPa
Process connection	G 1/2 B
Connector location	lower back mount
Materials	
Measuring system	copper alloy
Movement	Copper alloy
Dial	Aluminum, white
Pointer	standard pointer
Window	polycarbonate
Bezel ring	roll formed, stainless steel
Case filling fluid	glycerine
Operating conditions	
Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65
Options	
Mounting flange/bracket	front flange, stainless steel
Labelcode	
Label	WIKA standard without / with Tag-number
language of the label	German