



CorePro LEDlamps

CorePro LEDcandle 4-25W E14 827 B35 FR

Delivering a warm, halogen-like accent beam, LEDspots are a perfect fit for spot lighting and have a broad compatibility with transformers. LEDspots are compatible with most existing fixtures with a GU10 / MR16 GU5.3 / E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs. LEDcandle and LEDluster are compatible with existing fixtures with an E27/E14 holder and are designed for retrofit replacement of incandescent lamps. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

• General Characteristics

Cap-Base	E14
Bulb	B35 [B 35mm]
Bulb Finish	Frosted
Rated Lifetime (hours)	20000 hr
Rated Lifetime (years)	10 an

• Light Technical Characteristics

Color Code	827
Color Designation (text)	Warm White
Correlated Color Temperature	2700 K
Color rendering index	80
Color Temperature	2700 K [CCT 2700K]
Rated Luminous Flux	250 Lm

• Electrical Characteristics

Wattage	4 W
Wattage Technical	4 W
Voltage	220-240 V
Line Frequency	50 Hz
Power Factor	0.5 -
Lamp Current mA	35 mA
Dimmable	No
Wattage Equivalent	25 W
Starting Time	0.5 (max) s

• Environmental characteristics

Energy Efficiency Label (EEL)	Class A
-------------------------------	---------

• Measuring Conditions

Switching cycle	50000x
-----------------	--------

• Product Dimensions

Overall Length C	102 mm
Diameter D	35 mm

• Product Data



Order code	929000242302
Full product code	929000242302
Full product name	CorePro LEDcandle 4-25W E14 827 B35 FR
Order product name	CorePro LEDcandle 4-25W E14 827 B35 FR
Pieces per pack	1
Packing configuration	10
Packs per outerbox	10
Bar code on pack - EAN1	8718291677123
Bar code on outerbox - EAN3	8718291677130
Logistic code(s) - 12NC	929000242302
Net weight per piece	0.040 kg



PHILIPS

sense and simplicity

Dimensional drawing



E14

CorePro LEDcandle 4-25W E14 827 B35 FR

Product	C (Norm)	D (Norm)
LED 4-25W E14 827 B35 FR	102	35



© 2013 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2013, January 29
data subject to change