

DYMO®



LW Durable Labels

Industrial

DURABLE LABELS

Tear & Solvent Resistant

When confronted with challenging surfaces, use a label that's tougher and lasts longer than paper labels. DYMO LabelWriter Durable labels feature industrial-strength adhesive and a rugged coating that resists peeling and abrasion due to moisture and solvents.



LW Durable Label Features

- Industrial-strength adhesive sticks securely to challenging surfaces like metal tread plate, textured PVC, wood, glass, and more
- Protective coating prevents peeling from abrasion, as well as industrial oils and cleaners
- Moisture-resistant design withstands damp conditions up to 85% humidity
- Withstands a range of temperatures from -18°C to 50°C
- Ideal for labelling shelves, warehousing, chemical storage, floor markers, equipment/inventory, and more

Durability Properties



Moisture



Solvents



Oil



Textured Surfaces



Temperature
-18°C to 50°C

Compatible with...

LabelWriter 4XL
LabelWriter 450 Series¹



LW Durable Labels

Size	Label Count	Item Number
25 mm x 89 mm	700	1933081
25 mm x 25 mm	1700	1933083
57 mm x 32 mm	800	1933084
19 mm x 64 mm	900	1933085
104 mm x 159 mm	200	1933086*
59 mm x 190 mm	170	1933087
59 mm x 102 mm	300	1933088

*Only compatible with the LabelWriter 4XL

¹Not compatible with LabelWriter Duo



DYMO and the DYMO logo are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners.

Product of :
Newell Europe Sàrl
Chemin de Blandonnet, 10
CH 1214 Vernier, Switzerland

Represented in the EU by :
Newell Rubbermaid UK Services Limited,
Halifax Avenue – Fradley Park, Lichfield,
Staffordshire, WS13 8SS, United Kingdom
162890



We would love to hear from you
+442035648356
Consumer service :
www.dymo.com



www.dymo.com