

ACS480-04-050A-4



ACS480-04-050A-4 Pcont.max:22kW, lcont.max:48A

General Information

Global Commercial Alias	ACS480-04-050A-4
Product ID	3AXD50000199099
ABB Type Designation	ACS480-04-050A-4
EAN	6438177508533
Catalog Description	ACS480-04-050A-4 Pcont.max:22kW, lcont.max:48A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177508533
Invoice Description	ACS480-04-050A-4 Pcont.max:22kW, lcont.max:48A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

Dimensions

Product Net Height	240 mm
Product Net Weight	6.02 kg
Product Net Width	171.7 mm

Additional Information

Product Main Type	ACS480-04-050A-4
Product Name	Frequency Converter

Categories

Drives → Low voltage AC drives → General purpose drives

Water Utility Solutions → Desalination Plant → Electrical → Drive systems → Drives → Low voltage AC drives → General purpose drives

