

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight bulkhead cable jack (female)

24_TNC-50-2-1/133_N

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz

Interface and material data

Piece parts	Material	Plating
-------------	----------	---------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22543398	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description
22543398	24_TNC-50-2-1/133_NE

Suitable cables

Cable group	
	X3 - 2 mm / 50 Ohm

Suitable tools

Item number	Item description	Type of tool
22543112	74_Z-0-0-2	Spanner

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31321 / Date of publication: 12.07.2025 / uncontrolled copy