



DSCP-23 0240-PP4

Branch Connector 2-Pole, 3-Conductors/Pole, 0.2-4.0mm²



Product Properties:

Number of clamp positions (device side)	6 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	6 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12 mm
Colour	Multi-coloured
Operating temperature	-40-105 °C
Flammability rating (UL94)	V2

Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.2-4 mm ²
Nominal cross section (installation side)	0.2-4 mm ²
Cable diameter	1-4 mm

Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm ²
Conductor cross section solid (solid, stranded)	0.5-4 mm ²
Width	21 mm
Height	18 mm
Strip length	12 mm
MOQ	10 .
Unit	pck
Nominal cross section	0.2-4 mm ²
Length	19 mm
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Consumer pack
Search Description	FÖRGRENINGSKLÄMMA, 2-POL. 3-LEDARE/POL
Alternative SKU	DSCP-230240-PP4

Logistic information:

Barcode	733117643032
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	DSCP-23 0240-PP4
Taric code	85369010
Unit	pck

