



ENGLISH

Constant Current LED Driver 12 - 25vdc 20 Watt



The RS Pro Range of Dali Dimmable compact LED Drivers are suitable for indoor and are fully compliant to DALI control standard IEC62386 and have a logarithmic dimming range. We offer the range with a 3 year warranty as standard.

Features:

- Input Voltage 180-240VAC
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 3 Year Warranty
- CE Approved





ENGLISH

Specification				
Part Number	1766754			
Input Voltage Range	90-130V&180-240V/AC			
AC Frequency	48-62Hz			
Input current	0.26Amax			
Standby Power	0.5Wmax			
Output Mode	Constant Current			
Output Current	350mA	500mA	650mA	800mA
On Load Voltage	26-52V	20-40V	15-30V	12-25V
No Load Voltage	56V	45V	35V	30V
Output Power	20W Max.			
Power Factor	>0.95			
Efficiency	>80%			
Dimensions	107*40*22(mm)			
Weight	104g			
Operating Temperature	-30~45°C			
Storage Temperature	-40~+70°C			
Thermal Dissipation	Nature			
Relative Humidity	5~95%			
Isolation Voltage	In/Out 3750VAC			
Vibration	5-55Hz/2g,30 Minutes			
Life Time	50000Hours, at TC max			
EMI	EN55022, EN55015 Class B			
Safety	EN610598			
Electromagnetic Immunity	EN61547, ENV5024, EN61000-4-2/3/4/6/8/11			
Harmonic Current Emissions	EN61000-3-2, EN61000-3-3			