

433

hand taps, fine pitch, metric thread made from chrome-steel

DIN 2181 UNI 4535

• Set of 2 pieces

	art.	M	■ mm	L mm	L1 mm	⚖ g
004330201	433 6X0,75	6x0,75	4,5	48	16	30
004330202	433 7X0,75	7x0,75	4,5	56	18	37
004330203	433 8X0,75	8x0,75	5,0	50	16	42
004330204	433 8X1	8x1	5,0	56	16	42
004330205	433 9X0,75	9x0,75	6,0	63	22	34
004330206	433 9X1	9x1	6,0	63	22	54
004330207	433 10X0,75	10x0,75	6,5	63	18	67
004330208	433 10X1	10x1	6,5	63	18	66
004330209	433 10X1,25	10x1,25	6,5	63	18	64
004330210	433 11X0,75	11x0,75	7,0	70	25	61
004330211	433 11X1	11x1	7,0	70	25	87
004330212	433 11X1,25	11x1,25	7,0	70	25	87
004330213	433 12X0,75	12x0,75	7,0	70	20	93
004330214	433 12X1	12x1	7,0	70	20	94
004330215	433 12X1,25	12x1,25	7,0	70	20	94
004330216	433 12X1,50	12x1,5	7,0	70	20	94
004330217	433 14X1	14x1	8,0	80	32	126
004330218	433 14X1,25	14x1,25	8,0	80	32	126
004330219	433 14X1,50	14x1,5	8,0	80	32	126
004330220	433 16X1	16x1	10,0	80	32	162
004330221	433 16X1,50	16x1,5	10,0	80	32	164
004330222	433 18X1,50	18x1,5	11,0	95	40	270
004330223	433 18X2	18x2	11,0	80	25	199
004330224	433 20X1,5	20x1,5	14,5	80	22	246
004330225	433 22X1,5	22x1,5	14,5	80	22	331
004330226	433 24X1,5	24x1,5	14,5	80	22	430
004330227	433 24X2	24x2	14,5	80	22	416

