

**ZM100** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M100X2	Thread
D	130 mm	Outside diameter
h	20 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	465,000 N	Breaking load, axial
M _L	425 Nm	Breakawag
M _{AL}	250 Nm	Mounting torque reference
M _M	28.6 kg*cm ²	Mass moment of inertia
≈m	0.83 kg	Weight

Dimensions

d ₁	120 mm	Plant diameter outside
t	4 mm	Hight retaining slot
b	10 mm	Width retaining slot
c	10 mm	Distance bore
m	M8	Threaded - threaded pin