



Part Number : [1200680137](#)
Product Description : Micro-Change (M12)
Solid Body Splitter, 1 x 5-Pole Male to 2 x 5-
Pole Females, Black Overmold
Series Number : 120068
Status : Active
Product Category : Industrial Tees and
Splitters
Engineering Number : 0812-05EMF00001




Documents & Resources

Drawings
[1200680137_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Micro-Change (M12) Solid Body Splitter, 1 x 5-Pole Male to 2 x 5-Pole Females, Black Overmold
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678872687

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female

Temperature Range - Operating	-25°C to +90°C
-------------------------------	----------------