



PRODUCT-DETAILS

PHT0510

25MM GS-LSZH COAT CONDUIT 10M - BL

General Information	
Extended Product Type	PHT0510
Product ID	7TCA297020R0289
EAN	5011949004795
Catalog Description	25MM GS-LSZH COAT CONDUIT 10M - BL
Long Description	Liquid Tight, Pliable Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 27.3mm, Inside Diameter 20.4mm, Static Bend Radius 55mm, Reel Length 10 Meters, IP66, IP67 Rating, Galvanised Steel and Kraft Paper Core with Low Fire Hazard Jacket, Black

Additional Information	
Product Main Type	KOPEX-EX FLEXIBLE CABLE PROTECTION
Application	Indoors / Outdoors, Marine, Buildings, & Rail Infrastructure Where Low Smoke and Toxicity are of Concern

Ordering	
EAN	5011949004795
UPC	786210242552

Dimensions	
Outside Diameter	27.3 mm

Technical	
Number of Batteries	0
Color	Black
Material	Galvanized Steel with Kraft Paper Core and Low Fire Hazard Coating

Environmental	
WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information	
Package Level 1 Units	1 piece
Package Level 1 EAN	5011949004795
Package Level 1 Height	5.9 in 150 mm
Package Level 1 Depth / Length	16.14 in 410 mm
Package Level 1 Width	16.14 in 410 mm

Certificates and Declarations	
Declaration of Conformity - CE	9AKK107492A9617
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards	
ETIM 8	EC001179 - Protective metallic hose
ETIM 9	EC001179 - Protective metallic hose
UNSPSC	39131706

Categories
Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems