

8381SX
U bolts for pipes
AISI 304
LABORATORY TESTS

- chemical analysis

AVAILABLE CERTIFICATES

- Test report UNIEN10204 type 2.2



	art.	D mm	D gas	E mm
083810401	8381SX 11	11	1/8"	M6
083810402	8381SX 14	14	1/4"	M6
083810403	8381SX 18	18	3/8"	M6
083810404	8381SX 22	22	1/2"	M6
083810405	8381SX 27	27	3/4"	M6
083810406	8381SX 34	34	1"	M6
083810407	8381SX 43	43	1 1/4"	M6
083810408	8381SX 49	49	1 1/2"	M8
083810409	8381SX 61	61	2"	M8
083810410	8381SX 77	77	2 1/2"	M8
083810412	8381SX 89	89	3"	M8
083810413	8381SX 115	115	4"	M8
083810416	8381SX 168	168	6"	M10
083810418	8381SX 220	220	8"	M10