

Permanent Light 216 / Bulb

Bulb 7W BA15D 12V



Part No.: 955.015.34

MECHANICAL DATA

| | |
|-----------------------|--------|
| Height | 54 mm |
| Diameter | 16 mm |
| Housing colour | Silver |
| Weight with packaging | 10 g |
| Product weight | 8 g |

ELECTRICAL DATA

| | |
|-----------------------------|----------|
| Operating voltage | 12V |
| Operating voltage frequency | 50Hz |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 12 VDC |
| Rated operational current | 583 mA |
| Rated inrush current | 5.830 mA |
| Power illuminant | 7 W |

OPTICAL DATA

| | |
|---------------------|-------|
| Lamp fitting/socket | BA15d |
|---------------------|-------|

APPROVAL DATA

| | |
|-----------------------------|----|
| Conforms with CE | No |
| WEEE | No |
| Conforms with RED directive | No |
| Conform with ATEX-directive | No |
| Conforms with CCC | No |
| Conforms with FCC | No |
| Conforms with IC | No |
| EAC certificate available | No |
| Conforms with AS-I | No |
| ICAO Certification | No |
| Conforms with GL | No |
| Conforms with RoHS CN | No |



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.