



Main

Range of product	Odace
Aesthetic name	Odace Styl Pratic
Product or component type	Cover frame
Number of gangs	1 gang
Cover type	Lid Elastic membrane
Type of frame	Single
Type of packing	Flow-pack

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	White (RAL 9003)
Surface finish	Glossy
Material	ABS (acrylonitrile butadiene-styrene) SEBS
Height	102 mm
Width	91.4 mm
Depth	50.3 mm
Net weight	0.043 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EC EN 60669-1 IEC 60529 NF C 61-314 UNE 20315-1-1
Product certifications	LCIE: NF 603415B
IK degree of protection	IK04
IP degree of protection	IP44

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations