

B1210 - I-Robox Shoe S3 CI ESD SRC

Collection: Record

Upper: Nabutek Leather

Insole: Wire Lace System

Lining: SmellStop Antibacterial

Midsole: Fresh'n Flex

Toecap: SlimCap

Sole: PU/TPU

Outer Carton: 10

Record

Record antifatigue footwear collection offers an answer to the demand for lightweight design.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.



Standards

EN ISO 20345: 2011 S3 (CI ESD SRC)
EN 61340-4-3
EN 61340-5-1
CEI EN 61340-4-5

Features

- Overcap for a higher abrasion resistance
- Padded collar for added comfort
- Air Tech + TPU-Skin anti-fatigue sole with cushioning effect
- Anti-static footwear
- Shock absorption in the heel region
- Puncture resistant sole
- Cold insulation up to -17°C
- 200 joules resistant toe-cap
- Water resistant upper
- Hydrocarbons resistant
- Electronic devices protection from electrostatic discharges

B1210 - I-Robox Shoe S3 CI ESD SRC**Commodity Code: 6403993300****Test House**

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)

Via Alberto Riva Villasanta, 3

, Italy

Cert No: F-113-04666-21

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1210BKB35	Black/Blue	67.0	41.0	36.0	1.0400	0.0989	8052530120972	
B1210BKB36	Black/Blue	67.0	41.0	36.0	1.1100	0.0989	8050262509850	
B1210BKB37	Black/Blue	67.0	41.0	36.0	1.1500	0.0989	8050262509867	
B1210BKB38	Black/Blue	67.0	41.0	36.0	0.1800	0.0989	8050262509874	
B1210BKB39	Black/Blue	67.0	41.0	36.0	1.2300	0.0989	8050262509881	
B1210BKB40	Black/Blue	67.0	41.0	36.0	1.2700	0.0989	8050262509898	
B1210BKB41	Black/Blue	67.0	41.0	36.0	1.3100	0.0989	8050262509904	
B1210BKB42	Black/Blue	67.0	41.0	36.0	1.3500	0.0989	8050262509911	
B1210BKB43	Black/Blue	67.0	41.0	36.0	1.4000	0.0989	8050262509928	
B1210BKB44	Black/Blue	67.0	41.0	36.0	1.4600	0.0989	8050262509935	
B1210BKB45	Black/Blue	67.0	41.0	36.0	1.4900	0.0989	8050262509942	
B1210BKB46	Black/Blue	67.0	41.0	36.0	1.6000	0.0989	8050262509959	
B1210BKB47	Black/Blue	67.0	41.0	36.0	1.6900	0.0989	8050262509966	
B1210BKB48	Black/Blue	67.0	41.0	36.0	1.6600	0.0989	8050262509973	