



professionalLINE Cable Reel BQ IP44 33m H07BQ-F 3G2,5 *BE*



Basic data:

Product number: 9202334200
EAN: 4007123654604
Article type: KA 3214



Product information:

- Pro-reel with rollover protection on all sides.
- Stable on all four sides, perfect cable management from all four sides.
- Large, sturdy fold-down turning handle rolls cables in and out effortlessly.
- Sturdy carrying handles and plug storage compartments on all four sides.
- The body and reel are made of Rubbabren, an extremely shock- and impact-resistant plastic and rubber mix. For permanent use in toughest conditions.
- Cold-resistant to -25 °C.
- The BREMAXX®-PUR cable (BQ cable) is highly resistant to abrasions, crushing, UV light, cutting and tearing. In addition, it is acid-proof, oil-resistant, weatherproof and microbe-resistant. Remains highly flexible even at low temperature down to -40 °C.
- 4 water-jet protected earthed socket outlets with self-closing protective caps.
- With extra robust earthed plug.
- With thermal cut-out protection against overheating or overload.
- With visual readiness indicator in the socket insert.

Technical information

Cable: H07BQ-F 3G2,5

Cable colour: orange

Colour: black, grey, orange

Cable diameter: 2.5 mm²

Cable length: 33m

Max. current carrying capacity – e: 16 A

Cable quality: PVC / Plastic

Degree of protection (IP): IP44

Number of sockets: 4

Datasheet – 9202334200