



## Specification

VT7

Single pole voltage indicator



### Electrical

Audible and visual indication

Voltage range: 50V - 600V AC rms

Frequency range: 50 - 60Hz

Test current: <math><5\mu\text{A}</math>

### Environmental

Temperature (Operating & Storage):  $-10^{\circ}\text{C}$  to  $55^{\circ}\text{C}$

Humidity (Operating & Storage):  $\leq 85\%$  R.H.

Altitude: up to 2000m

### General

Power: 9V, PP3 alkaline battery (IEC 6LR61, NEDA 1604A)

Current consumption: 34mA max

Dimensions: 236(L) x 44(W) x 33(D) mm

Weight: 120g (battery included) approx

Includes: 9V PP3 battery, instructions

### Safety

Conforms to BS EN61010-1 CAT IV 300V, CAT III 600V

Class II, Double Insulation

Pollution Degree: 2

IP rating: IP54

Water resistant

### EMC

Conforms to BS EN61326-1