

Datasheet

RS Pro Right Angle 75Ω Cable Mount BNC Connector Plug, Crimp Termination URM 70

RS Stock No: **546-4178**



Product Details

RS Pro right angle cable mount BNC connector plug features copper contacts. This male connector plug has 50 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C.

Features and Benefits

- Copper contacts
- Crimp termination method
- Male connector



Specifications:

Body Orientation	Right Angle
Cable Type	URM 70
Contact Material	Copper
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Crimp
Standards Met	RoHS Compliant