

Features

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material Brass / Steel with Nickel Plated Finish
- DN5.5
- British Standard
- Single Shut Off System
- Flow 660l/min

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 309309



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Series 019 Quick Connect Couplings Plugs

Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material Brass / Steel with Nickel Plated Finish
- DN5.5
- British Standard
- Single Shut Off System
- Flow 660l/min

Specifications

Manufacturer Series	019
Coupling Type	Quick Connect Coupling Socket
Connection Standard	ISO 6150-C
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	35 bar
Flow	660l/min
Safety	2-Stage
Material	Stainless Steel
Finish	Plastic
Connection Type	Threaded
Thread Size	1/4 in
Thread Standard	G
Thread Gender	Female, Male
Coupling Gender	Female, Male
Threaded Connection	G 1/4in
Seal material	Nitrite Rubber
Hose Barb Connection	4mm

Specifications

