

The NT 65/2 Ap is a powerful, 2-motor wet and dry vac for professional applications. The suction power remains nearly constant due to the efficient cleaning of the flat pleated filter by blasts of air.

Standard accessories:

- Suction hose 4 m
- Metal suction tube
- 2 x 0.5 m
- Filter bag Paper
- Wet and dry floor tool 360 mm
- Crevice tool
- Drain hose (oil-resistant)
- Auto shutdown when max. level is reached
- Flat pleated filter Paper
- Bend
- Bumper bar
- Push handle
- Safety class II
- Castor with brake
- Maintenance-free suction turbines
2 piece



Order no.: 1.667-235.0

Technical data

Air flow rate (l/s)	2 x 74
Vacuum (mbar/kPa)	254/25.4
Container capacity (l)	65
Max. intake performance (W)	max. 2760
Standard nominal size (mm)	40
Cable length (m)	10
Sound level (dB(A))	73
Container material	Plastic
Frequency (Hz)	50-60
Voltage (V)	220-240
Weight (kg)	20
Dimensions (L x W x H) (mm)	600x480x920

Details

Description

The NT 65/2 Ap is a powerful wet and dry vac with the ApClean system, which ensures constant high suction power and long working intervals. The vacuum features a compact turbine housing with integrated filter cover for easily removing the large flat pleated filter. It is effectively cleaned with the help of the semi-automatic ApClean filter cleaning system. This ensures constant high suction power, longer working intervals and a long service life of the filter. The NT 65/2 Ap features electronic fill level detection for wet vacuuming. It prevents the maximum permitted fill level from being exceeded. The problem-free disposal of vacuumed fluids is made possible by the attached oil-resistant drain hose. Accessories can be quickly and easily connected to the vacuum using the clip system. The unit features a hose storage device, an accessory holder and a large tray e.g. for tools. The required mobility of the NT 65/2 Ap is provided by two large fixed wheels and two guide rolls.

Features & Benefits

On-board practical storage

Large on-board practical tool and accessory storage.

Integrated drain hose (oil-resistant)

Easily accessible drain hose for convenient liquid disposal.

ApClean (semi-automatic filter cleaning system)

Downtimes are very brief because of the clean filter.

Optimal suction power with high efficiency.

Hose and bend attachment

Convenient suction hose and bend attachment for easy transport and storage.

Accessories

Adapter (tube -> nozzle)

Adapter

From DN 40 to DN 61: Plastic adapter (electrically non-conductive). Suitable for NT vacuum cleaners.

Order no. 5.453-019.0



Adapter for electric power tools, clip on, el.

Power tool adapter C 35, el.

3-way plastic adapter. For DN 26 to DN 36. For connecting power tools to an industrial C or C-DN 35 suction hose. Suitable for NT vacuum cleaners.

Order no. 5.453-042.0



Power tool adapter C 35, electrically conductive

Inside Ø 25.4 mm, outside Ø 34.6 mm/ 38 mm, electrically conductive. Only NT vacuums.

Order no. 5.453-048.0



Connecting sleeve for electric tool C 35, el.

Inner Ø 28.6 mm, outer Ø 37.3 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-049.0



Power tool adapter C 35, electrically conductive

Inside Ø 27 mm, outside Ø 36.5 mm/38.8 mm, electrically conductive. Only NT vacuums.

Order no. 5.453-050.0



Adapter for electric power tools, clip on, el.

Connecting sleeve for electric tool C 35, el.
Inner Ø 32 mm, outer Ø 39 mm, el. Only NT-vacuums.
Order no. 5.453-051.0



Connecting sleeve for electric tools C 35, el.
Inner Ø 28 mm, outer Ø 34 mm/ 38.8 mm, el. Only NT-vacuums.
Order no. 5.453-052.0



Adapter for electric power tools, screwable

Power tool adapter, threaded, DN 35
3-way plastic adapter with fitting instructions. For DN 26 to DN 36. For connecting
to an industrial DN 35 suction hose.
Order no. 5.453-016.0



Power tool adapter, threaded, DN 35
Inside Ø 28.6 mm, outside Ø 37.3/38.8 mm.
Order no. 5.453-026.0



Power tool adapter, threaded, DN 35
Electrically conductive power tool adapter, threaded. Internal diameter: 32
mm. External diameter: 39 mm.
Order no. 6.902-059.0



Adapter for electric power tools, screwable

Power tool adapter, threaded, DN 35

2-way power tool adapter, threaded. For connecting to an industrial DN 35 suction hose. Internal diameter: 28 mm. External diameter: 34 mm and 38.8 mm Suitable for NT vacuum cleaners.

Order no. 6.902-095.0



All-purpose brushes

All-purpose brush

Natural bristles (ox hair), bristle element 120 x 45 mm.

Order no. 6.903-863.0



All-purpose nozzles (wet/dry)

All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 40) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.

Order no. 6.906-554.0



All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.903-018.0



All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle (DN 40) with 450 mm working width. With height-adjustable side rollers, brush strips (6.903-065.0) and oil-resistant squeegees (6.906-146.0). Only for NT vacuum cleaners.

Order no. 6.906-383.0



All-purpose nozzles (wet/dry)

All-purpose nozzle (wet and dry), DN 35

All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.906-384.0



All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 35) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.

Order no. 6.906-513.0



Bend metal

Bend, DN 35, metal

Robust, chromium-plated metal bend (DN 35), can be used instead of a plastic bend (with clip system adapter 5.407-112.0; C 35-DN 35, plastic, el.).

Order no. 6.900-519.0



Bend, DN 40, metal

Robust, chromium-plated metal bend (DN 40), can be used instead of a plastic bend (with clip system adapter 5.407-111.0; C 40-DN 40, plastic, el.).

Order no. 6.900-276.0



Bend stainless

Bend, stainless steel ID 35

Stainless steel and crooked, ID 35

Order no. 6.903-141.0



Bend stainless

Bend, stainless steel ID 40
Stainless steel and crooked, ID 40
Order no. 6.902-079.0



Car cleaning nozzles

Car vacuuming tool, DN 40
Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.
Order no. 6.900-952.0



Connecting sleeve C-DN (clip on taper), EL (electroconductive)

C-DN 35 adapter
C 35 hose connector for DN 35 accessory, electrically conductive.
Order no. 5.407-112.0



C 40 adapter
Electrically conductive adapter (C 40) with DN 35 connection for connecting DN 35 accessories to an industrial C 40 or C-DN 40 suction hose. Suitable for NT vacuum cleaners.
Order no. 5.407-109.0



C-DN 40 adapter
C 40 hose connector for DN 40 accessory, electrically conductive.
Order no. 5.407-111.0



Connecting sleeves

Adapter, ID 32/35, with internal thread

Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.

Order no. 6.902-077.0



Adapter, ID 40 with internal thread

Electrically non-conductive adapter with screw thread at both ends. For connecting 2 DN 40 suction hoses without connectors.

Order no. 6.900-286.0



Connecting sleeve, ID 61, with female thread

For connecting 2 suction hoses, thread on both sides

Order no. 6.902-078.0



Crevice nozzles

Crevice tool

Plastic crevice tool (DN 40) for vacuuming in crevices and corners. Length: 290 mm.

Order no. 6.903-033.0



Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 210 mm.

Order no. 6.900-385.0



Crevice nozzles

Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 370 mm.

Order no. 6.900-922.0



Crevice tool

Metal crevice tool (DN 40) for vacuuming in crevices and corners. Length: 400 mm.

Order no. 6.905-817.0



Crevice tools

Grout nozzle, synthetic

Grout nozzle, plastic, 370 mm

Order no. 6.900-222.0



Grout nozzle, stainless steel

Grout nozzle, stainless steel, 400 mm

Order no. 6.900-926.0



Extension hoses (Clip-system)

Extension hose, C 40

2.5 m electrically non-conductive standard extension hose for all C-40 hoses with clip system.

Order no. 6.906-344.0



Flat pleated filter (paper)

Flat pleated filter

Paper flat pleated filter (BIA-(U,S,G,C) dust class M) suitable for NT 65/2 Eco, NT 65/2 Eco Tc, NT 65/2 Eco Me.

Order no. 6.904-283.0



Flat pleated filter (PES)

Flat filters (PES)

Flat filter (PES) - BIA-(U,S,G,C) dust class M: rotproof polyester fleece, ideal for wet use and abrasives. Standard for NT 72/2 Eco Tc.

Order no. 6.904-284.0



Floor nozzles

Floor nozzle cpl. 500 mm

Aluminium, oil-proof, 500 mm, with height-adjustable rollers, strips (6.903-067.0) and rubber lips (6.906-168.1)

Order no. 4.130-413.0



HEPA filter for dust class H

HEPA surface filter

HEPA surface filter - dust class H (H 14) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.

Order no. 6.904-364.0



Membrane filter / fabric filter

Membrane filter / fabric filter

Polyester needle fleece membrane/fabric filter - BIA-C -, washable up to 40°C, metal fibres for earthing. Suitable for virtually all industrial two-motor NT vacuum cleaners.

Order no. 6.904-282.0



Miscellaneous

Extension cable

Extension cable, 20 m, 3x1.5 mm². With splash-proof earthing pin plug, strain relief and anti-kink sleeve.

Order no. 6.647-022.0



Other accessories for T and NT

Pre-separator

Complete container (80 litre) and lid (ID 61). For coarse dirt and fluids (without suction hose).

Order no. 3.864-010.0



Drum separator

Metal, from DN 61 to 61, only for liquids.

Order no. 3.864-012.0



Lid for separator

For 6.902-051.0/4.070-111.0 and NT 802 I container

Order no. 4.063-132.0



Other accessories for T and NT

Adapter ring for 200 l drum

Ring adapter for EURO steel drum (200 l) with lid but in connection with additional lid (separator) 4.063-132.0.

Order no. 6.902-051.0



Paper filter (2 ply)

Paper filter bags

5 3-ply, tear-resistant paper filter bags. BIA-(U, S, G, C) dust class M. For all NT 48/1, NT 65/2 Eco + Me and NT 72/2 Eco Tc models.

Order no. 6.904-285.0



Pipe dusting nozzles

Pipe dusting nozzle, ID 35

Plastic, pipe diameter 100 mm

Order no. 6.903-035.0



Pipe dusting nozzle

Plastic, pipe diameter 200 mm

Order no. 6.903-036.0



Plastic bend

Plastic bend

Plastic bend (DN 40) with C-40 clip system, suitable for all NT models.

Order no. 5.031-904.0



Plastic bend

Plastic bend

Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).

Order no. 5.031-718.0



Plastic bend

Electrically conductive plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models.

Order no. 5.031-939.0



Plastic bend

Electrically conductive plastic bend (DN 40) with C-40 clip system, suitable for all NT vacuum cleaners.

Order no. 5.032-427.0



Plastic sacks for dust-free disposal

Plastic sacks for dust-free disposal

PE plastic sack.

Order no. 6.900-698.0



Radiator brushes

Radiator brush

Radiator brush is suitable for crevice tool 6.900-385.0 or 6.905-240.0.

Order no. 6.903-034.0



Reducer (tube -> nozzle)

Reducer

Reducer for accessory extension. Ideal for accessories with DN 35 connecting cone in combination with accessories with DN 40 connecting cone.

Order no. 6.902-017.0



Reducer from ID 35 to 32

Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.

Order no. 6.902-072.0



Reducing sleeves

Reducer

Threaded reducer - from C-40 to DN 35. Suitable for NT vacuum cleaners.

Order no. 5.407-108.0



Reducer

Reducer (C 40 to C 35) for connecting accessories with C-35 clip connection to suction hoses with C 40 clip system.

Order no. 5.407-113.0



Repair kits

Repair set, C 40

Repair set (C40) includes threaded hose adapters (without bayonet adapter) for industrial NT vacuum cleaners with clip system.

Order no. 2.639-873.0



Repair kits

Repair kit, DN 61

Suction hose repair kit. Optional for all NT 65/2 and 72/2, NT 993 I, NT 802 I.

Order no. 2.862-038.0



Rubber suction tools, nose 45°

Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 35), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

Order no. 6.902-104.0



Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 40), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

Order no. 6.902-105.0




Rubber tool

Rubber nozzle, ID 40

Rubber.

Order no. 4.763-057.0



Set reducing / extension sleeves

Set of reducers/adaptor sleeves

DN 40/35, DN 35/32 (tube -> nozzle), plastic.

Order no. 2.860-117.0



Special filter bags, wet filter bags

Special filter bags, wet filter bags

Approved for dust class L, general cleaning, wet and dry, tear-resistant.

Order no. 6.904-252.0



Suction brushes

Suction brush

Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.

Order no. 6.903-862.0



Suction hoses (Clip-system)

Suction hose

4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.

Order no. 6.906-321.0



Suction hose (clip system), C 40, 10 m

10 m standard suction hose without bend and adapter. With bayonet at vacuum end and C 40 clip connection at accessory end.

Order no. 6.906-279.0



Suction hose

With bayonet and clip connection.

Order no. 6.906-714.0



Suction hoses (Clip-system)

Suction hose

Electrically conductive, 4 m suction hose with bayonet and C 40 clip connection.
Without bend and adapter.

Order no. 6.906-546.0



Suction hose (Clip-system), C 40, 16 m

With bayonet and clip connection.

Order no. 6.906-635.0



Suction hose (clip system), C 40, 10 m, el.

Suction hose with bayonet coupling, electrically conductive.

Order no. 6.906-877.0



Suction hoses complete

Suction hose, complete

4-m standard suction hose with DN 61 bayonet connector at the device end and
DN 61 tapered connector at the accessory end.

Order no. 4.440-264.0



Suction hose, complete

Industrial hose, PVC/elastomer with steel spiral, smooth inside

Order no. 4.440-328.0



Suction hoses complete

Suction hose, complete, ID 61, 10 m

10-m standard suction hose with DN 61 bayonet connector at the device end and DN 61 tapered connector at the accessory end.

Order no. 4.440-467.0



Suction hose, complete, DN 61, 4 m, oil-resistant

Oil-resistant.

Order no. 4.440-613.0



Suction hose, complete, DN 61, 10 m, oil-resistant

Oil-resistant.

Order no. 4.440-614.0



Suction hose complete, ID 61, 4 m, el.

Electrically conductive.

Order no. 4.440-616.0



Suction hose, complete

Electrically non-conductive 4.0m standard suction hose with bayonett at vacuum end and DN 40 cone at accessory end.

Order no. 4.440-263.0



Suction hose, complete

Oil-resistant

Order no. 4.440-303.0



Suction hoses complete

Suction hose, complete

Electrically non-conductive 10.0m standard suction hose with bayonett at vacuum end and DN 40 cone at accessory end.

Order no. 4.440-463.0



Suction hose complete

Electrically conductive, 10.0m, ID 40

Order no. 4.440-466.0



Suction hose, complete, DN 40, 10 m, oil-resistant
Oil-resistant.

Order no. 4.440-612.0



Suction hoses complete (Clip-system)

Suction hose

4 m electrically non-conductive suction hose with bend, bayonet at vacuum end and C 40 clip connection at accessory end. Without module.

Order no. 4.440-678.0



Suction hose, complete (clip system), C ID 40, 4 m

4 m electrically non-conductive suction hose with bend (C-DN 40) and module (4.060-474.0), bayonet at vacuum end and C 35 clip connection at accessory end.

Order no. 4.440-679.0



Suction hoses complete (Clip-system)

Suction hose, complete (clip system), C DN-40, + PFC module, electrically conductive

With bend and module (4.060-533.0), electrically conductive.

Order no. 4.440-728.0



Suction tubes metal

Suction tube

Chromium-plated metal suction tube (DN 40, 1x0.5 m), standard for virtually all two-motor industrial vacuum cleaners. Optional for industrial single-motor NT vacuum cleaners with DN 40 suction hose.

Order no. 6.900-275.0



Suction tube

Chromium-plated metal suction tube (DN 35, 1x0.5 m), standard for virtually all single-motor industrial NT vacuum cleaners.

Order no. 6.900-514.0



Suction tubes stainless steel

Suction tube, ID 40

Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.

Order no. 6.902-081.0



Suction tube

Stainless steel suction tube (DN 40, 1.0 m) only suitable for NT vacuum cleaners.


Order no. 6.906-531.0



Suction tubes stainless steel

Suction tube, DN 35

Order no. 6.902-154.0



Target group specific vacuum cleaner accessory sets

Professional cleaning kit ID 40

Individual parts: Suction hose 4 m (4.440-263.0), bend, metal (6.900-276.0), suction tube 2 x 0.5 m, metal (6.900-275.0), grout nozzle (6.903-033.0), floor nozzle with rollers (6.903-051.0).

Order no. 2.637-353.0



Car cleaning kit

Target group-specific accessory nozzles in DN 35 for interior cleaning of vehicles, upholstery & fixtures.

Order no. 2.862-166.0



Industry set

Target group-specific robust complete accessory set in DN 61 for vacuuming coarse dirt in industry, construction etc.

Order no. 2.637-355.0



Chip cleaning kit

Target group-specific robust connection set in DN 61 for cleaning in conjunction with oil-resistant suction hose and rubber nozzle.

Order no. 2.640-760.0



Target group specific vacuum cleaner accessory sets

Bus kit

Accessory kit for vacuuming and cleaning buses, train compartments, etc., in combination with the recommended NT vacuum cleaner.

Order no. 2.640-560.0



Tools for vacuuming smaller areas, cleaning machines

45° rubber suction nozzle

Angled 45°, for suction of machines, oil-resistant

Order no. 6.902-106.0



Tools for vacuuming surfaces / cleaning machines

Aluminium surface nozzle

Flat surface nozzle cpl. DN 51, 200 mm, aluminium with brush and stainless steel bumper

Order no. 4.130-415.0



Metal scratcher and scraper nozzle

Scratcher and scraper tool DN 61, sheet metal, 117 mm

Order no. 6.903-360.0



Y-adapter kit

Y-adapter kit

Plastic distributor - suitable for NT vacuum cleaners.

Order no. 2.637-217.0

