



XXLCamera G3



5 m
DOF 1...6 cm

Universal micro camera for inspections over average distances

Rev 0617



- **Problem locating:** the camera indicates what is behind or in objects, walls circuits or cables etc. even under worst light conditions, due to the LED-lighting.
- **Ideal for difficult accessibility areas** due to the small measuring head (ø 9 mm)
- **Waterproof camera head and cable**
- Powerful object lighting thanks to **4 high-performance LEDs**

TECHNICAL DATA

CAMERA HEAD / CABLE ø 9 mm, IP 68 (immersion depth 1,5 m, 60 min.)
CAMERA FOCUS F1 cm - F6 cm
CAMERA RESOLUTION 640 x 480 pixels
CABLE DIAMETER 6 mm
LENGTH OF FLEX CABLE 5 m
OPERATING TEMPERATURE 0°C ... 45°C
STORAGE TEMPERATURE -10°C ... 60°C
WEIGHT 650 g
DIMENSIONS (W x H x D) 5000 mm x 17 mm x 17 mm

Only for VideoFlex G3.



Camera head (ø 9 mm) with LED-Lighting



XXLCamera G3

Packing dimension (W x H x D)
215 x 60 x 215 mm

ARTICLE	ARTICLE NO.	EAN CODE	PU
XXLCamera G3	082.219A	4 021563 698851	2

CAMERA 640 x 480 pixel **LED LIGHT** **IP 68**