



Cut



Medium Duty

Medium-duty cut and abrasion-resistant gloves, offering high comfort and dexterity

- **Enhanced dexterity:** These comfortable high-dexterity gloves are designed with a seamless liner and knitted wrist to ensure a good level of flexibility and close fit, and may also be worn as an underglove
- **Improved durability:** EDGE[®] 48-700 cut protection work gloves feature a reinforced thumb crotch that increases abrasion resistance and wear life
- **Food handling compliance:** In addition, these food gloves comply with FDA food handling requirements and the Commission Regulation (EC) No. 1935/2004 as well as the Regulation (EC) No. 2023/2006 related to Good Manufacturing Practices (GMP) for materials and articles intended to come in contact with foodstuffs



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Food Processing

Applications

- Slicing, cutting and shopping
- Cleaning and changing slicer blades in delis and supermarkets
- Defeathering and skinning
- Assembly and finishing
- Body assembly
- Machine tool operation
- Sheet metals and metalwork

Key Features

- **Seamless liner and knitted wrist:** Added dexterity for meticulous work
- **Reinforced thumb crotch:** Durable work gloves with abrasion resistance
- **FDA-approved food handling gloves:** Superb safety and hygiene standards

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X4XC

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
EDGE [®] 48-700	Liner Material: Polyethylene, Wrapped Yarn, Fiber glass, Polyester, Spandex Cuff Style: Knitwrist	13	5, 6, 7, 8, 9, 10, 11	200-260MM, 7.87-10.24 INCHES	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699