

CRIMPFOX CENTRUS 6H-NC - Crimping pliers



1202883

<https://www.phoenixcontact.com/in/products/1202883>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping tool, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Clear view into the crimping area

Commercial data

Item number	1202883
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	BH3131
GTIN	4063151267384
Weight per piece (including packing)	459.8 g
Weight per piece (excluding packing)	375.73 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX CENTRUS 6H-NC - Crimping pliers



1202883

<https://www.phoenixcontact.com/in/products/1202883>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4
---------	--------------------------

Product properties

Product type	Crimping tool
Compression	HEX crimp
Product property	Unlockable pressure lock
	Low grip span
	Up to 30% lower actuation force
	Clear view into the crimping area

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	26
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 6 mm ² (2 x 0.5 mm ² ... 2 x 4 mm ²)
Cross section range AWG	26 ... 10 (2 x AWG 20 ... 2 x AWG 12)

Dimensions

Width	65 mm
Height	22 mm
Length	175 mm

Material specifications

Color	black/green
-------	-------------

CRIMPFOX CENTRUS 6H-NC - Crimping pliers



1202883

<https://www.phoenixcontact.com/in/products/1202883>

Classifications

ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX CENTRUS 6H-NC - Crimping pliers



1202883

<https://www.phoenixcontact.com/in/products/1202883>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CRIMPFOX CENTRUS 6H-NC - Crimping pliers



1202883

<https://www.phoenixcontact.com/in/products/1202883>

Accessories

CRIMPFOX/ SPR-4 - Replacement spring

1200288

<https://www.phoenixcontact.com/in/products/1200288>

Spare recuperating spring



CRIMPFOX CENTRUS NC/U-HANDLE - Replacement handle

1202880

<https://www.phoenixcontact.com/in/products/1202880>

Replacement upper handle for CRIMPFOX CENTRUS series



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in