



CSB P W 165 x 15.87 x 1.6 x 24ATB

CIRCULAR SAW BLADES FOR HAND HELD CIRCULAR SAWS

- PTFE coating: Cuts cooler, non stick for quicker cuts. Protects against corrosion and accumulation of resin.
- Laser cut vibration slots: Low vibration and increased accuracy.
- High grade laser cut steel: Guaranteed accuracy.
- Premium cobalt infused tungsten carbide: Sharp and clean cuts.
- Thin Kerf: Cordless optimised, extra thin cutting width for maximum runtime
- All wood types: Soft/ hardwood, plywood, laminated chipboard, melamine, MDF
- **Standard blades without PTFE coating and vibration slots



All Wood Types	✓
Article Number	4932471311
Blade diameter (mm)	165
Bore size (mm)	5/8"
Cutting width (kerf) (mm)	1.6
Hook Angle	+15°
Materials suited for	Wood with nails & screws Green wood Wood Particleboard, Fibrecement board, Fibreglass
No. of teeth	24
Pack quantity	1
Thin Kerf	✓
Tooth Form	ATB