



2-1375191-2 | JACK,SL110,RJ45,CAT5E,BLK

Body Features

110 Block Material Polycarbonate

Configuration Features

Keyed No
Number of Positions 8
Wiring Pattern Universal

Contact Features

Contact Base Material Beryllium copper
Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness 50.00 μin | 1.27 μm

Dimensions

Conductor Outside Diameter 0.057 in | 1.45 mm
Solid Wire Range .51 mm² | .65 mm²
Stranded Wire Range .14 mm² | .2 mm²
Wire Range 22 AWG | 24 AWG | 26 AWG

Housing Features

Housing Color Black
Housing Material Polycarbonate

Industry Standards

UL Flammability Rating UL 94V-0

Mechanical Attachment

Mounting Type SL Series Faceplate

Other

Comment With strain relief.

Packaging Features

Packaging Method Poly Bag
Packaging Quantity 25

2-1375191-2 | JACK,SL110,RJ45,CAT5E,BLK

Product Availability

Region | Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

| | |
|----------------------|-------------------------|
| Product Type | Connector - Modular |
| Performance Category | Category 5e |
| Shielded | No |
| System | SL 110 Series |
| Applies To | Panel |
| Cable Type | Unshielded Twisted Pair |
| Connector Style | Jack |
| Connector Type | Connector Assembly |
| Dust Cover | Without |
| Jack Type | RJ45 |

Termination Features

| | |
|----------------------------------|-------------------------------------|
| Termination Method to Wire/Cable | Insulation Displacement Crimp (IDC) |
| Termination Style | 110 Style Punch-Down |

Regulatory Compliance/Certifications

| | |
|-----------------|-----------------------|
| Agency | Classification |
| RoHS 2011/65/EU | Compliant |