

# GWS 9-115 P Professional


PROtection Angle grinder



## The new series of PROtection angle grinders

Robust, perfect handling and outstanding user safety

LI-ION



Specification	
Rated Input Power	900 W
No-load speed	11,500 rpm
Disc Diameter	115mm
Grinding spindle thread	M14
Battery Voltage	18 V
Wire cup brush, diameter	75mm
Rubber backing pad, diameter	115mm
Part number	0601790260

Key Product Features	Consumer Benefit
Compact Design	Weighs only 2.1 kg, for comfortable working, especially in tight spaces and overhead
Increased Cable Lifetime	Due to improved cable grommet
Outstanding user protection	thanks to the anti-rotation protective guard - stands firm, even if the disc breaks
Electronic Motor Protection	EMP protects the motor against overload and ensures a long lifetime
Electronic Cell Protection	Protects the battery against overload, overheating and deep discharge
3 year tool warranty and 2 year battery warranty*	100% consumer confidence



Cutting



Grinding

\*\* Compared to a 3.0 Ah battery without CoolPack technology



**You Tube** [youtube.com/BoschProfessionalUK](https://www.youtube.com/BoschProfessionalUK)

**f** [facebook.com/BoschProfessionalPowerToolsUK](https://www.facebook.com/BoschProfessionalPowerToolsUK)



**BOSCH**

Invented for life

\* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide