



J1 40A LP-PP1

Japanese Fuse Links, 40A, Green

Product Properties:

Explosion-proof	No
Release characteristic	Time-lag (T)
Rated voltage	58 V
Optical defect indication	Yes
Type of current	DC
Colour code	Blue
Nominal voltage DC	58 V
Max. continuous voltage DC	58 V
Number of fuses	1 .
Model	Other
Max. current (Imax)	40 A
Nominal current	40 A

Dimensions:

Width	12.1 mm
MOQ	10 .
Unit	pck
Rated voltage	58 V
Mounting holes	Other
Thickness	10 mm
Length	16 mm

Approvals:

Compliance:

Conflict Minerals	Contain "Tin"
POPs	No POPs
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC004122 - Strip fuse
ETIM-Release	DYNAMIC
Trademark	NECORE
Product Group	Japanese fuse links - Pin-pac
Search Description	JAPANSÄKRING, 40A
Alternative SKU	J140ALP-PP1

Logistic information:

Barcode	733117611764
Country of origin	JP
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	J1 40A LP-PP1
Taric code	85361050
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.