

# HAMMER DRILL XR 18V 4AH LI-ION BRUSHLESS

- 2-speed, all-metal transmission, increased efficiency and durability
- 3-position LED lamp with up to 77 lumens
- 15 different torque settings for optimal precision
- Switch provides intelligent variation in drilling speed and greater control
- 13 mm self-locking all-metal chuck
- Percussion mode for drilling through hard materials

No-load speed (rpm): 0-550/2000  
Beats per Minute (cps/min) : 0-9350/34000  
Ø wood/metal/concrete drilling (mm):  
40/13/13  
Chuck Capacity (mm): 1.5-13



With 2 batteries, charger, belt clip, magnetic bit holder

DCD796M2-QW

5 035 048 725 450