



PRODUCT INFORMATIONS

Application

Analogue balanced audio links.
For fixed and mobile applications.
For inside wiring of racks and audio equipment.
Studio cabling.

Electrical properties

Max. voltage : **250 V**
Test voltage : **1500 V**
Admissible intensity : **1,5 A**
Conductor resistance at 20 °C : **< 85,9 Ω/km**
Insulation resistance at 20 °C : **> 500 MΩ.km**

Characteristics

 Temperature range :
- 20 °C → + 85 °C

 Minimum bending radius :
Static : 30 mm
Dynamic : 45 mm

 Kg/Km **15** Weight :
15 kg/km

 **RoHS**
COMPLIANT Conform to RoHS directive