



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1623244-1
CRG0805 1% 51K

TE Part #1676694-2
RN 0805 40R2 0.1% 10PPM 1K RL

TE Part #3-2199250-3
Shield Finger, Loose Piece, Type C, 3.2 h

TE Part #9-1625868-0
RP 2A 0.25W 45R3 0.1% 25PPM 1K RL

TE Part #1969818-1
09P UMNL PIN HDR ASSY NATL, PIN V0 GW

TE Part #5-104178-6
10 SYS 50 HDR SRST UNSHRD SN

TE Part #2118726-2
STD SHIELD FRAME, CRS-44.37X44.37X9.75MM

TE Part #2007464-3
SFP+ 1x1 Cage Assy, PF,with Heatsink

TE Part #2-2176238-5
CPF A 0805 270R 0.1% 25PPM 5K RL

TE Part #7-2176367-3
RQ 0603 26K1 0.1% 10PPM 1K RL

Documents

- CAD Files

Customer View Model

[ENG_CVM_CVM_1879029-2_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1879029-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1879029-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[SMD Trimmers - Type 3213 Series - Tyco Electronics Passives](#)

English

3213X102M

3213 1K

