



# 10 mm 3/8" impact socket deep - 1 pc

## SHOCKWAVE™ IMPACT DUTY IMPACT SOCKETS

- SHOCKWAVE™ IMPACT DUTY steel (Chrome-Molybdenum) is high quality alloy steel which provides ultimate strength and durability.
- Best fitting thanks to 6 gripping points.
- Non-slip hex geometry to prevent socket and fastener rounding.
- Deep wall construction provides clearance for protruding bolts.
- Stamped and ink filled diameter markings and laser etched part number for wear resistance.
- Dual hole design and groove for security accessories.



|                            |             |
|----------------------------|-------------|
| ø (mm)                     | 15.8        |
| Article Number             | 4932480284  |
| For anchor rod thread size | M6          |
| Pack quantity              | 1           |
| Size AF [across flats][mm] | 10          |
| Tool reception             | 3/8" square |
| Total length (mm)          | 65          |
| Working depth [mm]         | 4.6         |
| Working length (mm)        | 4.6         |