

Datasheet

RS Pro Natural Acetal Sheet, 610mm x 305mm x 6.3mm

RS Stock No: **350-6236**



Product Details

RS Pro acetal sheet in natural colour, measures 610 x 305 x 6.3 mm and is permanently antistatic with low surface and volume resistivity. It has low co-efficient of friction and clean room acceptable. It is unaffected by moisture and with good impact properties. It is Ideal for components that may experience frictional or fluid flow static charges.

Features and Benefits

- Permanently antistatic with low surface and volume resistivity
- Low co-efficient of friction and clean room acceptable
- Unaffected by moisture and with good impact properties
- Ideal for components that may experience frictional or fluid flow static charges
- Comes in natural colour

Specifications:

Colour	Natural
Flammability Rating	UL 94 HB
Material	Acetal
Polymer Type	Copolymer
Density	1.33 g/cm ³
Elongation	25%
Length	610 mm
Maximum Operating Temperature	+100°C
Thickness	6.3 mm
Water Absorption	0.8%
Width	305 mm
Tensile Strength	45 MPa