

213.53.063 250 bar 2nd scale psi G1/4B lower mount

Bourdon tube pressure gauges, liquid filled,

Item number: 9626951

Quantity: 1 pcs.

Order code: 213.53-C-BG525P-GB-UZZZ-ZZ# 53 31ALZNZ2 ZA-ZZ4
DIAL-IAC1ZZZ#ZZZZZ1Z- 1Z1ZZ41ZZZ
LABEL-E01DE-ZZZZZ

Overview: 213.53.063 250 bar 2nd scale psi G1/4B lower mount
class 1.6
Window: plastic, clear
Case filling fluid: glycerine
Single packing closed with adhesive tape and
yellow RS-label with NR. 110876 (client's part
number) on side of the package
single packing
stop-pin at zero
2nd scale red
EN 837-1 *Cl.1.6* *UKCA* *CE* model * ... * *ps: ...* *WIKA* Dial after WN 12.006
GB2

Details: Bourdon tube pressure gauges, liquid filled,
stainless steel case, model 213.53.050/063
Model: 213.53
Specifications according to data sheet: PM 02.12
Measuring system: copper alloy
Case: stainless steel 1.4301
Case: Crimp ring case (version 53)
Nominal size: 063 mm
Scale range: 0...250 bar
2nd Scale or Special Scale: 2nd scale psi
Process connection: G 1/4 B
Connector location: lower mount
Additional ordering information: Single packing closed with adhesive tape and
yellow RS-label with NR. 110876 (client's part
number) on side of the package
Accuracy class: class 1.6
Overpressure safe: standard
Case filling fluid: glycerine
Pointer: plastic, black (double division)
Window: plastic, clear
Packaging: single packing
Dial: plastic, white, with stop-pin
Dial description:
Pressure Gauge Standard: International (standard Europe)

Date: 22/01/2024



color for 1.scale (outside): black
color for 2.scale (inside): red RAL 3020
dial background: White
individual text for dial: Dial after WN 12.006 GB2
Manufacturer logo: *WIKA*
stop pin on dial: at zero
norm-mark on dial: *EN 837-1*
accuracy class on dial: *Cl.1.6*
CE mark on dial: *UKCA* *CE* model * ... *