

434
serie di 2 maschi a mano sgrossatore e finitore passo fine in acciaio HSS
DIN 2181 UNI 4535

• serie di 2 pezzi

	art.	M	■ mm	L mm	L1 mm	g
004340001	434 6X075	6x0,75	5,2	50	15	39
004340003	434 8X075	8x0,75	7,2	56	18	40
004340004	434 8X1	8x1	7,0	56	18	43
004340007	434 10X075	10x0,75	9,2	63	20	37
004340008	434 10X1	10x1	9,0	63	18	57
004340009	434 10X125	10x1,25	8,7	70	24	61
004340014	434 12X1	12x1	11,0	70	20	92
004340015	434 12X125	12x1,25	10,7	70	20	92
004340016	434 12X150	12x1,5	10,5	70	20	92
004340017	434 13X150	13x1,5	11,5	70	22	89
004340018	434 14X1	14x1	13,0	70	20	96
004340019	434 14X125	14x1,25	12,7	70	20	95
004340020	434 14X150	14x1,5	12,5	70	20	95
004340021	434 15X150	15x1,5	13,5	70	22	109
004340022	434 16X1	16x1	15,0	70	20	117
004340023	434 16X150	16x1,5	14,5	70	20	116
004340024	434 18X150	18x1,5	16,5	80	22	172
004340025	434 18X2	18x2	16,0	80	22	170
004340026	434 20X125	20x1,25	18,8	80	22	218
004340027	434 20X150	20x1,5	18,5	80	22	219
004340028	434 20X2	20x2	18,0	80	22	220
004340029	434 22X150	22x1,5	20,5	80	22	275
004340030	434 24X1	24x1	23,0	90	22	337
004340031	434 24X150	24x1,5	22,5	90	22	331
004340032	434 24X2	24x2	22,0	90	22	330

